

UNIT		CONDENSER		EVAPCO, INC. evapco	DWG. #	WB3242410-DRD-ST	REV.	-
MODEL #		ATC-2002E	SCALE		NTS	SERIAL #		DATE
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]								
FACE B PLAN VIEW					FACE C (4) ACCESS DOOR FACE D			
FACE A					FACE A			
SHIPPING WEIGHT 75540 lbs+ [34265] kg+ OPERATING WEIGHT 103480 lbs+ [46940] kg+ HEAVIEST SECTION WEIGHT 16090 lbs+ [7300] kg+ NO. OF SHIPPING SECTIONS 6 DRAWN BY: SLR								