


|                                      |              |                                                                                                        |                            |                   |
|--------------------------------------|--------------|--------------------------------------------------------------------------------------------------------|----------------------------|-------------------|
| UNIT<br><b>CLOSED CIRCUIT COOLER</b> |              | <b>EVAPCO, INC.</b>  | DWG. #<br>WB3242010-DRC-SF | REV.<br>-         |
| MODEL #<br>ATWB 24-5N20-Z            | SCALE<br>NTS |                                                                                                        | SERIAL #                   | DATE<br>11/9/2025 |


NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]


  







|                                           |                                            |                                                   |                               |                  |
|-------------------------------------------|--------------------------------------------|---------------------------------------------------|-------------------------------|------------------|
| SHIPPING WEIGHT<br>60060 lbs+ [27245] kg+ | OPERATING WEIGHT<br>94480 lbs+ [42860] kg+ | HEAVIEST SECTION WEIGHT<br>25520 lbs+ [11580] kg+ | NO. OF SHIPPING SECTIONS<br>4 | DRAWN BY:<br>JLG |
|-------------------------------------------|--------------------------------------------|---------------------------------------------------|-------------------------------|------------------|