



UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WB3242010-DRC-SF	REV. -
MODEL # ATWB 24-5020-Z	SCALE NTS		SERIAL #	DATE 11/8/2025


NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]





FACE B



FACE A

SHIPPING WEIGHT 60080 lbs+ [27255] kg+	OPERATING WEIGHT 94500 lbs+ [42865] kg+	HEAVIEST SECTION WEIGHT 25530 lbs+ [11585] kg+	NO. OF SHIPPING SECTIONS 4	DRAWN BY: JLG
---	--	---	-------------------------------	------------------