


UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WB3242406-DRD-SF	REV. -
MODEL # ATWB 24-3K24-Z	SCALE NTS		SERIAL #	DATE 3/14/2026

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [MM]

FACE C




(4) ACCESS DOOR


FACE B

PLAN VIEW

FACE D

FACE A





FACE B

SHIPPING WEIGHT

57580 lbs+ [26120] kg+

OPERATING WEIGHT

92080 lbs+ [41770] kg+

HEAVIEST SECTION WEIGHT

11600 lbs+ [5265] kg+

NO. OF SHIPPING SECTIONS

6

DRAWN BY: JLG