UNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC. Evapco			DWG. # WV	DWG. # WV050604-DRD-SF	
MODEL #	LRWB 5-2F6-Z	SCALE NTS	EVAP	CO, TINC		SERIAL #		DATE 11/4/2025
2. MPT DI FPT DE BFW D GVD D FLG DE PE DE! 3. +UNIT ACCES 4. 3/4" [19 RECOM 5. DIMEN 6. * - APP USE FC CONNE 7. MAKE- 20 psi [8. SERIES	AN MOTOR LOCATION ENOTES MALE PIPE THRE ENOTES FEMALE PIPE THRE ENOTES BEVELED FOR W ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLU ESORIES (SEE ACCESSOR' EMM] DIA. MOUNTING HOLI MMENDED STEEL SUPPOR SIONS LISTED AS FOLLOW PROXIMATE DIMENSIONS DOR PRE-FABRICATION OF ECTING PIPING. UP WATER PRESSURE 137 kPa] MIN, 50 psi [344 kF S FLOW PIPING AND AUX. ARE BY OTHERS	READ ELDING JDE Y DRAWINGS) ES. REFER TO ET DRAWING VS: ENGLISH FT IN [METRIC] [mm] OO NOT	FACE B PLAN VIEW	5'-5/8"	FACE	12'-2 7/8"		FACE D
							6'-3"	
1'-4 [4	4 3/8" * -	2'-4" *			(2) 1/2" [15] FPT VENT	[6'-3" 1905]	
	4" [100] BFW FLUID IN [100] BFW FLUID OUT		1'-0" * 3'-7 1/2" [1106]		— SERIES FLOW PIPING (BY OTHERS)		$\overline{\mathbb{R}}$	
3 <u>1</u> 83	(3) /4" TYP		6'-7 3/4" [2026] [324] * [919]		AUX. CROSSOVER DRAIN (BY OTHERS) ACCESS DOOR			6'-7 3/4" [2026]
	8" [80] MPT OVERFLOW	1'-8 7/8" [530]	8 3/4" [222]	-	5'-6" [1676]	-1" [25] MPT MAKE-UP	(h)	1'-8 1/8" [511] ACCESS DOOR
2		5'-5/8" 1540]		1'-1 5/8"	FACE	12'-2 7/8" [3731]	•	_