


UNIT	CLOSED CIRCUIT COOLER			DWG. #	WV050604-DRD-SF	REV.
MODEL #	eco-LRWB 5-2F6-Z	SCALE NTS		SERIAL #		DATE 1/31/2026


NOTES:

1. (M) - FAN MOTOR LOCATION
2. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING
5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN
[METRIC] [mm]
6. * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF
CONNECTING PIPING.
7. MAKE-UP WATER PRESSURE
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX
8. SERIES FLOW PIPING AND AUX. CROSSOVER
DRAIN ARE BY OTHERS

FACE B **PLAN VIEW**



DWG. #	WV050604-DRD-SF	REV.	-
SERIAL #		DATE	1/31/2026



SHIPPING WEIGHT 3660 lbs+ [1665] kg+ OPERATING WEIGHT 5780 lbs+ [2625] kg+ HEAVIEST SECTION WEIGHT 3660 lbs+ [1665] kg+ NO. OF SHIPPING SECTIONS 1 DRAWN BY: