


UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WB3090908-DRC-ST	REV. -
MODEL # eco-ATWB 9-4J9	SCALE NTS		SERIAL #	DATE 3/26/2026

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]

FACE B

PLAN VIEW




FACE C

ACCESS DOOR

FACE A

FACE D

FACE B



1'-9 3/8" [543]

4'-3 3/4" [1238]

2'-2 3/8" [670]

7'-7" [2313]

11'-10 7/8" [3629]

2'-3" [686]

(2) 4" [100] BFW

FLUID IN

FLUID OUT

2" [50] MPT MAKE-UP

1'-11 1/8" [589]

3" [76]

5 1/4" [133]

4 1/4" [108]

5'-7 1/4" [1708]

8'-5 1/2" [2578]

6" [154]


4'-3 7/8" [1316]

1'-3" [383]

2" [50] MPT DRAIN

3" [80] MPT OVERFLOW

FACE A



1'-7/8" [327]

(2) 1/2" [15] FPT VENT

1'-3 5/8" [397]

8'-11 1/2" [2730]

SHIPPING WEIGHT	11210 lbs+ [5085] kg+	OPERATING WEIGHT	15610 lbs+ [7085] kg+	HEAVIEST SECTION WEIGHT	9770 lbs+ [4435] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY:	SLR
-----------------	-----------------------	------------------	-----------------------	-------------------------	----------------------	--------------------------	---	-----------	-----