





UNIT		CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. #		WB3242406-DRD-ST		REV.		-						
MODEL #		eco-ATWB 24-3J24			SCALE		NTS		SERIAL #		DATE		7/12/2026				
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]																	
FACE B PLAN VIEW					FACE C  FACE D FACE A  FACE A												
FACE B 					FACE A 												
SHIPPING WEIGHT		68140 lbs+ [30910] kg+		OPERATING WEIGHT		102640 lbs+ [46560] kg+		HEAVIEST SECTION WEIGHT		14240 lbs+ [6460] kg+		NO. OF SHIPPING SECTIONS		6		DRAWN BY: SLR	