

UNIT		CONDENSER		EVAPCO, INC. 	DWG. #	WB3171206-DRD-ST	REV.	-
MODEL #	eco-ATC-580A	SCALE	NTS		SERIAL #		DATE	6/21/2026

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS UPPER SECTION

3. MPT DENOTES MALE PIPE THREAD

FPT DENOTES FEMALE PIPE THREAD

BFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED

FLG DENOTES FLANGE

PE DENOTES PLAIN END

4. +UNIT WEIGHT DOES NOT INCLUDE

ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. MAKE-UP WATER PRESSURE

20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. *-APPROXIMATE DIMENSIONS DO NOT USE

FOR PRE-FABRICATION OF CONNECTING

PIPING

7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO

RECOMMENDED STEEL SUPPORT DRAWING.

8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN

METRIC [mm]

FACE B

PLAN VIEW

FACE C

FACE D

FACE A

SHIPPING WEIGHT

23780 lbs+ [10790] kg+

OPERATING WEIGHT

31860 lbs+ [14455] kg+

HEAVIEST SECTION WEIGHT

10020 lbs+ [4545] kg+

NO. OF SHIPPING SECTIONS

4

DRAWN BY:

SLR