

UNIT		CONDENSER		<div>EVAPCO, INC.</div> <div><div>evapco</div></div>	DWG. #		WB3242808-DRC-ST		REV.		-					
MODEL #		eco-ATC-2292A			SCALE		NTS		SERIAL #		DATE		7/15/2025			
<div>NOTES:</div> <div>1. (M)- FAN MOTOR LOCATION</div> <div>2. HEAVIEST SECTION IS UPPER SECTION</div> <div>3. MPT DENOTES MALE PIPE THREAD</div> <div>    FPT DENOTES FEMALE PIPE THREAD</div> <div>    BFW DENOTES BEVELED FOR WELDING</div> <div>    GVD DENOTES GROOVED</div> <div>    FLG DENOTES FLANGE</div> <div>    PE DENOTES PLAIN END</div> <div>4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)</div> <div>5. MAKE-UP WATER PRESSURE</div> <div>    20 psi MIN [137 kPa], 50 psi MAX [344 kPa]</div> <div>6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING</div> <div>7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.</div> <div>8. DIMENSIONS LISTED AS FOLLOWS:</div> <div>    ENGLISH FT-IN</div> <div>    METRIC [mm]</div>																
<div>FACE B</div> <div>PLAN VIEW</div>					<div>FACE C</div> <div>(4) ACCESS DOOR</div> <div>FACE D</div>											
<div>FACE B</div>					<div>FACE A</div>											
<div>SHIPPING WEIGHT</div> <div>92480 lbs+ [41950] kg+</div>					<div>OPERATING WEIGHT</div> <div>124620 lbs+ [56530] kg+</div>					<div>HEAVIEST SECTION WEIGHT</div> <div>20010 lbs+ [9080] kg+</div>			<div>NO. OF SHIPPING SECTIONS</div> <div>6</div>		<div>DRAWN BY:</div> <div>SLR</div>	