





UNIT		CONDENSER		EVAPCO, INC. 		DWG. # WB3244008-DRC-ST		REV. -									
MODEL # eco-ATC-3315A		SCALE NTS				SERIAL #		DATE 7/22/2025									
<p>NOTES:</p> <p>1. (M)- FAN MOTOR LOCATION</p> <p>2. HEAVIEST SECTION IS UPPER SECTION</p> <p>3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END</p> <p>4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)</p> <p>5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]</p> <p>6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING</p> <p>7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.</p> <p>8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]</p>						<p>FACE C</p>  <p>FACE D</p>											
<p>FACE B</p> <p>PLAN VIEW</p>				<p>FACE A</p> 													
 <p>FACE B</p>				<p>FACE A</p>													
SHIPPING WEIGHT		129380 lbs+ [58690] kg+		OPERATING WEIGHT		175520 lbs+ [79615] kg+		HEAVIEST SECTION WEIGHT		27810 lbs+ [12615] kg+		NO. OF SHIPPING SECTIONS		6		DRAWN BY: SLR	