

UNIT CLOSED CIRCUIT COOLER  
MODEL # ESW4 12-34N18X-LF

EVAPCO, INC. 

DWG. # WX41218X3608F-DRA-ST  
SERIAL #

REV -  
DATE: 2/13/2026

NOTES:  
1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS COIL SECTION

3. MPT DENOTES MALE PIPE THREAD

FPT DENOTES FEMALE PIPE THREAD

BFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED

FLG DENOTES FLANGE

4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. 3/4" [19MM] DIA. MOUNTING HOLES.

REFER TO RECOMMENDED STEEL  
SUPPORT DRAWING

6. MAKE-UP WATER PRESSURE


20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

7. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN  
[METRIC] [mm]

8. \* - APPROXIMATE DIMENSIONS DO NOT USE  
FOR PRE-FABRICATION OF CONNECTING PIPING


9. COIL CONNECTIONS LOCATED ON FACES B AND D



FACE B



FACE B & D  
COIL CONNECTIONS



FACE A