

UNIT COOLING TOWER		<div>EVAPCO, INC.</div> <div>evapco</div>	DWG. # T3091136-DRD-ST	REV. -
MODEL # AT 19-3J11	SCALE NTS		SERIAL #	DATE 9/12/2025

NOTES:
1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO
RECOMENDED STEEL SUPPORT DRAWING.
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE B

PLAN VIEW

FACE C

FACE D

FACE A

1'-9 3/8" [543]

(M)

1'-7/8" [327]

2" [51]

8'-1/2" [2451]

12'-4 3/8" [3769]

4'-3 7/8" [1318]

8'-5 1/2" [2578]

3/8" [9]

FACE B

8'-7 1/8" [2619]

5'-2 3/4" [1594]

2" [50] MPT MAKE-UP

8" [200] BFW/GVD INLET

3" [80] FPT OVERFLOW

3" [80] FPT DRAIN

8" [200] BFW/GVD OUTLET

1'-11 1/8" [587]

1'-2 7/8" [378]

7 1/2" [190]

3 5/8" [92]

5 1/4" [133]

9" [229]

5'-2 3/4" [1594]

10'-5 1/2" [3188]

FACE A

SHIPPING WEIGHT	5120 lbs+ [2325] kg+	OPERATING WEIGHT	8420 lbs+ [3820] kg+	HEAVIEST SECTION WEIGHT	3520 lbs+ [1600] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY:	JLG
-----------------	----------------------	------------------	----------------------	-------------------------	----------------------	--------------------------	---	-----------	-----