



| | | | | |
|------------------------------|--------------|--|---------------------------|-------------------|
| UNIT COOLING TOWER | | EVAPCO, INC.  | DWG. # T3170936-DRG-ST | REV. - |
| MODEL # AT 217-3H9 | SCALE NTS | | SERIAL # | DATE 7/19/2025 |

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE C




(2) ACCESS DOOR


FACE B

FACE D

FACE A

PLAN VIEW





FACE B

FACE A

| | | | | | | | | | |
|-----------------|----------------------|------------------|-----------------------|-------------------------|----------------------|--------------------------|---|-----------|-----|
| SHIPPING WEIGHT | 9040 lbs+ [4105] kg+ | OPERATING WEIGHT | 14720 lbs+ [6680] kg+ | HEAVIEST SECTION WEIGHT | 2980 lbs+ [1355] kg+ | NO. OF SHIPPING SECTIONS | 4 | DRAWN BY: | KDS |
|-----------------|----------------------|------------------|-----------------------|-------------------------|----------------------|--------------------------|---|-----------|-----|