

UNIT COOLING TOWER		<div>EVAPCO, INC.</div> <div>evapco</div>	DWG. # T3091136-DRD-ST	REV. -
MODEL # AT 19-3H11	SCALE NTS		SERIAL #	DATE 9/12/2025

NOTES:
1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO
RECOMENDED STEEL SUPPORT DRAWING.
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE B

PLAN VIEW

FACE C

FACE D

FACE A

1'-9 3/8" [543]

(M)

1'-7/8" [327]

2" [51]

8'-1/2" [2451]

12'-4 3/8" [3769]

4'-3 7/8" [1318]

8'-5 1/2" [2578]

3/8" [9]

FACE B

8'-7 1/8" [2619]

5'-2 3/4" [1594]

2" [50] MPT MAKE-UP

3" [80] FPT OVERFLOW

3" [80] FPT DRAIN

8" [200] BFW/GVD INLET

8" [200] BFW/GVD OUTLET

1'-11 1/8" [587]

1'-2 7/8" [378]

7 1/2" [190]

3 5/8" [92]

5 1/4" [133]

9" [229]

5'-2 3/4" [1594]

10'-5 1/2" [3188]

FACE A

SHIPPING WEIGHT	5020 lbs+ [2280] kg+	OPERATING WEIGHT	8320 lbs+ [3775] kg+	HEAVIEST SECTION WEIGHT	3420 lbs+ [1555] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY:	JLG
-----------------	----------------------	------------------	----------------------	-------------------------	----------------------	--------------------------	---	-----------	-----