


UNIT COOLING TOWER		EVAPCO, INC. 	DWG. # T3121436-DRE-ST	REV. -
MODEL # AT 112-3I14	SCALE NTS		SERIAL #	DATE 1/31/2026

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE C




FACE B


FACE D

FACE A

PLAN VIEW



FACE B



FACE A

SHIPPING WEIGHT	8890 lbs+ [4035] kg+	OPERATING WEIGHT	16220 lbs+ [7360] kg+	HEAVIEST SECTION WEIGHT	6020 lbs+ [2735] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY: KDS
-----------------	----------------------	------------------	-----------------------	-------------------------	----------------------	--------------------------	---	---------------