

UNIT		COOLING TOWER		<div>EVAPCO, INC.</div> <div><div>evapco</div></div>	DWG. #	T3170948-DRG-ST	REV.	-	
MODEL #		AT 217-4G9			SCALE	NTS		SERIAL #	DATE

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS UPPER SECTION

3. MPT DENOTES MALE PIPE THREAD

FPT DENOTES FEMALE PIPE THREAD

BFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED

FLG DENOTES FLANGE

4. +UNIT WEIGHT DOES NOT INCLUDE

ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. MAKE-UP WATER PRESSURE

20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. 3/4" [19MM] DIA. MOUNTING HOLES.

REFER TO RECOMMENDED STEEL SUPPORT

DRAWING

7. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN

[METRIC] [mm]

FACE C

(M)

(2) ACCESS DOOR