UNIT CONDENSER				EVADCO 1		vapco	DWG. # CEWR122010-DRA-ST	REV	-
eco-PMRC-995 SCALE NTS		;	EVAPCO, INC. Evapeo			SERIAL#	12/14/2025		
2. MPT DENOTI FPT DENOTI FPT DENOTI BFW DENOT GVD DENOTI PE DENOTI PE DENOTI ACCESSORI A. 3/4" [19mm] [RECOMMEN 50 psi [344 kf 6. DIMENSIONS ENGLISH F [METRIC] [n 7. * - APPROXIM	S PLAIN END HT DOES NOT INCLUDE ES (SEE ACCESSORY DRAWINGS DIA. MOUNTING HOLES. REFER TO DED STEEL SUPPORT DRAWING. ATER PRESSURE 20 psi [137 kPa] Pa] MAX. S LISTED AS FOLLOWS: T-IN	O MIN,			FACE B PLAN VIEW		FACE C		FACE D
	3'-0 7/8" * [937] (2) 4* [100	D) PE		3'-3 1/4" [997] *	6'-6 1/8" [1984]				
2"[50] MPT MAKE UP 3"[80] MPT DRAIN 2'-5"[737]			- Q	15'-0 1/2" [4585] 9'-11" [3023] *	8'-6 3/8" [2600]				
1'-8" [508]				3"[80] MPT OVERFLOW	2'-3 1/4" [692]-		20'-0 1/4" [6102]		
SHIPPING WEIGHT	41230 lbs+ [18705] kg+	FACE	PERATING WEIGHT	49300 lbs+ [22365] kg+	HEAVIEST SECTION WEIGHT	31900 lbs+ [14470] kg+	FACE A NO. OF SHIPPING SECTIONS 2	DRAWN BY:	JLG