CONDENSER			FVADCO	TNC	Vanco	CEWR122012-DRA-ST	REV -
MODEL#	eco-PMRC-1026	SCALE NTS	EVAPCO,	TIAC' A		SERIAL#	DATE: 12/14/2025
2. MPT DENO FPT DENO BFW DENO GVD DENO FLG DENO PE DENOT! 3. +UNIT WEI ACCESSOF 4. 3/4" [19mm] RECOMMI 5. MAKE-UP V 50 psi [344 6. DIMENSION ENGLISH [METRIC] 7. **- APPROX	NS LISTED AS FOLLOWS: FT-IN	R TO IG. a] MIN,		FACE B PLAN VIEW		FACE A	FACE D
3'-0 7/8" * 5'-8 5/8" * [1743]							
		0	O	7'-2 5/8" [2200]			
2"[50] MP1 MAKE UF 3"[80	OVERSIZED ACCESS DOORS 5 1/8" [130]		9'-11" [3023] *	8'-6 3/8" [2600]			
1'-8" [5 3	7/8" [08]	4" [121] 7'-4 3/8" [2245] 11'-10 3/8" [3616]	3"[80] MPT OVERFLOW	2'-3 1/4" [692]–		20'-0 1/4" [6102]	
		FACE B				FACE A	
SHIPPING WEIGHT	46860 lbs+ [21260] kç	OPERA WEIG	тіng нт 55100 lbs+ [24995] kg+	HEAVIEST SECTION WEIGHT	37530 lbs+ [17025] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: JLG