

EVAPCO, INC.




UNIT	CLOSED CIRCUIT COOLER	MODEL #	eco-LRWB 3-3E6-Z	SCALE	NTS	DWG. #	W2243608-MRC-ST	REV.		DATE	6/22/2025	SERIAL #	
------	-----------------------	---------	------------------	-------	-----	--------	-----------------	------	--	------	-----------	----------	--

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
5. 19mm DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE-137 kPa MIN, 344 kPa MAX
7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

PLAN VIEW



FACE 1

(8) 15 FPT VENTS



FACE 2

SHIPPING WEIGHT	45415	kg +	OPERATING WEIGHT	72120	kg	HEAVIEST SECTION WEIGHT	9530	kg	NO. OF SHIPPING SECTIONS	6
-----------------	-------	------	------------------	-------	----	-------------------------	------	----	--------------------------	---