




UNIT	eco-LRWB 5-5M12-Z
TITLE	EXTERNAL SERVICE PLATFORM

EVAPCO, INC.



DWG. #	PLWZ0912-DA
SCALE	N.T.S.
DRAWN BY	SLR

MODEL #	H DIM	
	FT-IN	[mm]
ESWA 102-23H, 23I	8'-4"	2540
ESWA 102-24H, 24I	8'-11 1/2 "	2731
ESWA 102-25H, 25I	9'-7"	2921
ESWA 102-26H, 26I	10'-2 1/2 "	3112
ESWA 102-33H, 33I, 33J, 33K	9'-4"	2845
ESWA 102-34H, 34I, 34J, 34K	9'-11 1/2 "	3035
ESWA 102-35H, 35I, 35J, 35K	10'-7"	3226
ESWA 102-36H, 36I, 36J, 36K	11'-2 1/2 "	3416
ESWA 102-43I, 43J, 43K	10'-4"	3150
ESWA 102-44I, 44J, 44K	10'-11 1/2 "	3340
ESWA 102-45I, 45J, 45K	11'-7"	3531
ESWA 102-46I, 46J, 46K	12'-2 1/2 "	3721



NOTES:

1. LADDER AND PLATFORM SHIP LOOSE. FIELD INSTALLATION BY OTHERS IS REQUIRED.
2. THE BOTTOM OF THE LADDER DOES NOT EXTEND PAST THE BASE OF THE UNIT.
IF THE UNIT IS ELEVATED THEN AN OPTIONAL EXTENDED LADDER PACKAGE SHOULD BE CONSIDERED. (CONSULT FACTORY)
3. REFER TO RIGGING PACK FOR LADDER AND PLATFORM MOUNTING INSTRUCTIONS.
4. EACH PLATFORM AND LADDER ASSY. WEIGHS 650 LBS. [295 KG]
5. MODELS ESWA 102-23H, 23I, 102-24H, 24I, AND 102-33H, 33I, 33J, 33K DO NOT REQUIRE AN INTERMEDIATE LADDER BRACKET.

6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN
[METRIC] mm