



UNIT	eco-LRWB 8-5K9-Z	EVAPCO, INC. 	DWG. #	LDWZ0912DA	
TITLE	SLOPED LADDER INSTALLATION PACKAGE		SCALE	N.T.S.	DRAWN BY SLR



LADDER SHIPS
LOOSE FOR FIELD
MOUNTING
(BY OTHERS)



NOTE:

- REFER TO RIGGING PACK FOR LADDER AND PLATFORM MOUNTING INSTRUCTIONS.
- (M)-FAN MOTOR LOCATION
- DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN
[METRIC] [mm]

* THE BOTTOM OF THE LADDER IS AT THE BASE OF THE UNIT. IF THE UNIT IS ELEVATED THEN A LADDER EXTENSION SHOULD BE CONSIDERED. (CONSULT FACTORY).
LADDER EXTENSIONS OF UP TO 3 FEET CAN BE ADDED WITHOUT ANY ADDITIONAL SUPPORT. FOR A LADDER EXTENSION LONGER THAN 3 FEET ADDITIONAL SUPPORT MUST BE PROVIDED BY OTHERS.

RIG LADDER BEFORE PIPING UNIT

MODEL #	X DIM	
	FT-IN	[mm]
ESWA 102-23H, 23I	4' -6 3/4 "	1391
ESWA 102-24H, 24I	4' -8 5/8 "	1438
ESWA 102-25H, 25I	4' -9 3/8 "	1457
ESWA 102-26H, 26I	5' - 1/2 "	1537
ESWA 102-33H, 33I, 33J, 33K	4' -8 5/8 "	1438
ESWA 102-34H, 34I, 34J, 34K	4' -9 3/8 "	1457
ESWA 102-35H, 35I, 35J, 35K	5' - 1/2 "	1537
ESWA 102-36H, 36I, 36J, 36K	5' -2 7/8 "	1597
ESWA 102-43I, 43J, 43K	4' -11 3/4 "	1518
ESWA 102-44I, 44J, 44K	5' -2 7/8 "	1597
ESWA 102-45I, 45J, 45K	5' -3 5/8 "	1616
ESWA 102-46I, 46J, 46K	5' -4 1/2 "	1638

CUSTOMER INSTALLATION NOTES:

- REMOVE LADDER BRACKET MOUNTING BOLTS (1) FROM LADDER MOUNTING CHANNELS (2) ON PAN CASING SECTIONS.
- LOOSEN, BUT DO NOT REMOVE, LADDER BRACKET ASSY. BOLTS (3).
- TO ASSEMBLE, SLIDE LADDER BRACKET ASSY. (4) OVER LADDER MOUNTING CHANNELS (2) LOCATED ON PAN AND CASING (DO NOT REMOVE LADDER BRACKET ASSY. (4) FROM LADDER.)
- ALIGN HOLES AND REINSTALL LADDER BRACKET MOUNTING BOLTS (1) THROUGH LADDER BRACKET ASSY. (4) AND LADDER MOUNTING CHANNELS (2).
- TIGHTEN ALL BOLTS.
- TIGHTEN ADJUSTING SCREW (5) IN THE ADJUSTABLE MOUNTING BRACKETS WHEN APPLICABLE.

