




# EVAPCO, INC.



|      |                       |         |       |                 |      |      |          |
|------|-----------------------|---------|-------|-----------------|------|------|----------|
| UNIT | CLOSED CIRCUIT COOLER | MODEL # | SCALE | DWG. #          | REV. | DATE | SERIAL # |
|      |                       |         | NTS   | W2241406-ERC-RS |      |      |          |

## NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING
- + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
- 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- THE SPRAY PUMP SHOULD BE SIZED FOR 1800 GPM AND 2.5 PSIG AT THE INLET CONNECTION
- \*- APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING



|                 |       |        |                  |       |      |                         |       |      |                          |   |
|-----------------|-------|--------|------------------|-------|------|-------------------------|-------|------|--------------------------|---|
| SHIPPING WEIGHT | 33680 | lbs. + | OPERATING WEIGHT | 45440 | lbs. | HEAVIEST SECTION WEIGHT | 13880 | lbs. | NO. OF SHIPPING SECTIONS | 4 |
|-----------------|-------|--------|------------------|-------|------|-------------------------|-------|------|--------------------------|---|