

UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WB36M1206-DRC-ST	REV. -
MODEL # eco-ATWB 20-3L12	SCALE NTS		SERIAL #	DATE 10/10/2025

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]

FACE C

(2) ACCESS DOOR

FACE B

PLAN VIEW

FACE D

FACE A

Dimensions include: 1'-10 1/4" [565], 2'-1 1/4" [643], 3 5/8" [92], 20'-5 5/8" [6112], 2'-6 3/8" [772], 8'-3 5/8" [2532], 14'-5 7/8" [4416], 6'-2 1/4" [1884], 3'-10" [1168], 1'-5" [433], 9'-4 1/2" [2858], 9'-5 1/2" [2883], 9'-9 3/4" [2991], 5 1/8" [130], 2'-11 1/4" [643], 1'-3 1/4" [387], 1'-5" [432], 11'-11 3/4" [3651].

Connections include: (4) 4" [100] BFW, (2) 2" [50] MPT MAKE-UP, (2) 3" [80] MPT DRAIN, (2) 3" [80] MPT OVERFLOW, (4) 1/2" [15] FPT VENT.

FACE B

FACE A

SHIPPING WEIGHT	29640 lbs+ [13445] kg+	OPERATING WEIGHT	44660 lbs+ [20260] kg+	HEAVIEST SECTION WEIGHT	12260 lbs+ [5565] kg+	NO. OF SHIPPING SECTIONS	4	DRAWN BY:	SLR
-----------------	------------------------	------------------	------------------------	-------------------------	-----------------------	--------------------------	---	-----------	-----