

CONFIDENTIAL

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.


EVAPCO, INC.



TITLE INTAKE/DISCHARGE DUCTWORK

UNIT: ALL 4X LS UNITS

DWG. # DWAC04ML-DB



- NOTES:
- 1. THE MAXIMUM EXTERNAL STATIC PRESSURE OF THE INTAKE AND DISCHARGE DUCT SHOULD NOT EXCEED 1/2" W.G.
 - 2. SOLID BOTTOM PANELS WILL BE REQUIRED IF THE UNIT IS NOT MOUNTED DIRECTLY ON THE FLOOR.
 - 3. MOTOR AND FAN BEARINGS LUBRICATION FITTINGS ARE ACCESSIBLE THRU THE ACCESS DOOR ON THE INSIDE OF THE INTAKE DUCTWORK.
 - 4. INLET SCREENS TO BE PROVIDED BY OTHERS ON INLET DUCT WORK APPLICATIONS.
 - 5. M IS FOR MOTOR LOCATION. ON 18' UNIT THE MOTOR IS IN THE MIDDLE.