


EVAPCO, INC.



| | | | | | | | | | | | | | |
|------|-----------------------|---------|--------------|-------|-----|--------|---------------------|------|--|------|----------|----------|--|
| UNIT | CLOSED CIRCUIT COOLER | MODEL # | eco-PMC-1225 | SCALE | NTS | DWG. # | WX12124810-ERB-LFHR | REV. | | DATE | 6/9/2025 | SERIAL # | |
|------|-----------------------|---------|--------------|-------|-----|--------|---------------------|------|--|------|----------|----------|--|

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS LOWER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
4. + UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE SEPARATE DRAWINGS
FOR ACCESSORIES)
5. 3/4" DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT
DRAWING
6. THE SPRAY PUMP SHOULD BE SIZED FOR 850
GPM AND 3.5 PSIG AT THE INLET CONNECTION
7. *- APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING



| | | | | | | | | | | |
|-----------------|-------|--------|------------------|-------|------|-------------------------|-------|------|--------------------------|---|
| SHIPPING WEIGHT | 17305 | lbs. + | OPERATING WEIGHT | 21655 | lbs. | HEAVIEST SECTION WEIGHT | 10925 | lbs. | NO. OF SHIPPING SECTIONS | 2 |
|-----------------|-------|--------|------------------|-------|------|-------------------------|-------|------|--------------------------|---|