


EVAPCO, INC.




UNIT	EVAPORATIVE CONDENSER	MODEL #	eco-PMC-855	SCALE	NTS	DWG. #	C2122408-MRB-SLF	REV.	DATE	SERIAL #
------	-----------------------	---------	-------------	-------	-----	--------	------------------	------	------	----------

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
5. 19mm DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE-137 kPa MIN, 344 kPa MAX
7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.
8. MAKE-UP IS LOCATED 121mm FROM EACH CONNECTION END.



PLAN VIEW



FACE 1



FACE 2

SHIPPING WEIGHT	16190	kg +	OPERATING WEIGHT	22570	kg	HEAVIEST SECTION WEIGHT	6940	kg	NO. OF SHIPPING SECTIONS	4
-----------------	-------	------	------------------	-------	----	-------------------------	------	----	--------------------------	---