



# EVAPCO, INC.



| UNIT                         | MODEL #        | SCALE | DWG. #            | REV. | DATE     | SERIAL # |
|------------------------------|----------------|-------|-------------------|------|----------|----------|
| <b>CLOSED CIRCUIT COOLER</b> | LSWE 10-6N36-Z | NTS   | W2241808-MRB-LFHF |      | 6/8/2025 |          |

## NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING
4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
5. 19mm DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE-137 kPa MIN, 344 kPa MAX
7. \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.



|                 |       |      |                  |       |    |                         |      |    |                          |   |
|-----------------|-------|------|------------------|-------|----|-------------------------|------|----|--------------------------|---|
| SHIPPING WEIGHT | 23140 | kg + | OPERATING WEIGHT | 36450 | kg | HEAVIEST SECTION WEIGHT | 9780 | kg | NO. OF SHIPPING SECTIONS | 4 |
|-----------------|-------|------|------------------|-------|----|-------------------------|------|----|--------------------------|---|