

# EVAPCO, INC.




|      |                       |         |                     |       |        |        |                   |      |   |      |           |          |  |
|------|-----------------------|---------|---------------------|-------|--------|--------|-------------------|------|---|------|-----------|----------|--|
| UNIT | EVAPORATIVE CONDENSER | MODEL # | ATC-DC-1228L-25-1EF | SCALE | N.T.S. | DWG. # | EGCH122802-DRC-ST | REV. | - | DATE | 8/26/2025 | SERIAL # |  |
|------|-----------------------|---------|---------------------|-------|--------|--------|-------------------|------|---|------|-----------|----------|--|

## NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
7. \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

**FACE 2  
PLAN VIEW**




**FACE 1**



**FACE 2**

CROSSOVER  
PIPING  
(BY OTHERS)



**FACE 1**

|                 |                        |                  |                        |                         |                       |                          |   |           |     |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|
| SHIPPING WEIGHT | 37500 lbs+ [17010] kg+ | OPERATING WEIGHT | 53680 lbs+ [24350] kg+ | HEAVIEST SECTION WEIGHT | 14900 lbs+ [6760] kg+ | NO. OF SHIPPING SECTIONS | 6 | DRAWN BY: | SFR |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|