

UNIT		CONDENSER		EVAPCO, INC. evapco	DWG. #	WB3242410-DRD-ST		REV.	-																																								
MODEL #		ATC-1879E			SCALE	NTS		SERIAL #	DATE 1/12/2026																																								
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]																																																	
FACE B PLAN VIEW					FACE C (4) ACCESS DOOR FACE D																																												
FACE A					FACE A																																												
FACE B					FACE A																																												
SHIPPING WEIGHT 75300 lbs+ [34160] kg+										OPERATING WEIGHT 103240 lbs+ [46830] kg+										HEAVIEST SECTION WEIGHT 16030 lbs+ [7275] kg+										NO. OF SHIPPING SECTIONS 6										DRAWN BY: SLR									