


UNIT COOLING TOWER		<div>EVAPCO, INC.</div> <div></div>	DWG. # T3TM1224-DRD-ST	REV. -
MODEL # AT 110-2M12	SCALE NTS		SERIAL #	DATE 9/10/2025

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS UPPER SECTION

3. MPT DENOTES MALE PIPE THREAD

FPT DENOTES FEMALE PIPE THREAD

BFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED

FLG DENOTES FLANGE

4. +UNIT WEIGHT DOES NOT INCLUDE

ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. MAKE-UP WATER PRESSURE

20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO

RECOMENDED STEEL SUPPORT DRAWING.


7. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN

[METRIC] [mm]


FACE B

PLAN VIEW



FACE C


ACCESS DOOR



FACE D


FACE B

FACE A



FACE A

FACE C



SHIPPING WEIGHT

6890 lbs+ [3130] kg+

OPERATING WEIGHT

11850 lbs+ [5380] kg+

HEAVIEST SECTION WEIGHT

4470 lbs+ [2030] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

JLG