


|                        |              |                                                                                                            |                           |                  |
|------------------------|--------------|------------------------------------------------------------------------------------------------------------|---------------------------|------------------|
| UNIT<br>COOLING TOWER  |              | <div>EVAPCO, INC.</div>  | DWG. #<br>T3121248-DRD-ST | REV.<br>-        |
| MODEL #<br>AT 112-4L12 | SCALE<br>NTS |                                                                                                            | SERIAL #                  | DATE<br>2/7/2026 |

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 3/4" [19MM] DIA. MOUNTING HOLES.  
REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]

**FACE C**





**FACE D**

**FACE B**

**PLAN VIEW**

**FACE A**





**FACE B**

|                 |                      |                  |                       |                         |                      |                          |   |           |     |
|-----------------|----------------------|------------------|-----------------------|-------------------------|----------------------|--------------------------|---|-----------|-----|
| SHIPPING WEIGHT | 8530 lbs+ [3870] kg+ | OPERATING WEIGHT | 14740 lbs+ [6690] kg+ | HEAVIEST SECTION WEIGHT | 6130 lbs+ [2785] kg+ | NO. OF SHIPPING SECTIONS | 2 | DRAWN BY: | KDS |
|-----------------|----------------------|------------------|-----------------------|-------------------------|----------------------|--------------------------|---|-----------|-----|