


UNIT COOLING TOWER		EVAPCO, INC. 	DWG. # T3121248-DRD-ST	REV. -
MODEL # AT 112-4I12	SCALE NTS		SERIAL #	DATE 9/21/2025


NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE B



FACE A



SHIPPING WEIGHT

8360 lbs+ [3795] kg+

OPERATING WEIGHT

14570 lbs+ [6610] kg+

HEAVIEST SECTION WEIGHT

5960 lbs+ [2705] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

KDS