

# EVAPCO, INC.






|                              |              |       |                  |      |            |          |
|------------------------------|--------------|-------|------------------|------|------------|----------|
| UNIT                         | MODEL #      | SCALE | DWG. #           | REV. | DATE       | SERIAL # |
| <b>CLOSED CIRCUIT COOLER</b> | ATWB 24-4L18 |       | WB3241808-DRA-ST |      | 12/16/2025 |          |

## NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING

## FACE 2 PLAN VIEW



|                 |                        |                  |                        |                         |                       |                          |   |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|
| SHIPPING WEIGHT | 47880 lbs+ [21718] kg+ | OPERATING WEIGHT | 76220 lbs+ [34573] kg+ | HEAVIEST SECTION WEIGHT | 20020 lbs+ [9081] kg+ | NO. OF SHIPPING SECTIONS | 4 |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|