


|                                      |              |  |                            |                   |
|--------------------------------------|--------------|--|----------------------------|-------------------|
| UNIT<br><b>CLOSED CIRCUIT COOLER</b> |              | <b>EVAPCO, INC.</b>  | DWG. #<br>WB3241206-DRD-SF | REV.<br>-         |
| MODEL #<br>ATWB 24-3J12-Z            | SCALE<br>NTS |  | SERIAL #                   | DATE<br>9/15/2025 |


NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]


**FACE C**

(2) ACCESS DOOR




**FACE B**

**PLAN VIEW**




**FACE D**

**FACE A**






**FACE B**



**FACE A**

|                 |                        |                  |                        |                         |                       |                          |   |           |     |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|
| SHIPPING WEIGHT | 28500 lbs+ [12930] kg+ | OPERATING WEIGHT | 45740 lbs+ [20750] kg+ | HEAVIEST SECTION WEIGHT | 11540 lbs+ [5235] kg+ | NO. OF SHIPPING SECTIONS | 4 | DRAWN BY: | JLG |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|