JNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC. EVGPCO SERIAL #		DWG. # WV030608-DRD-SF	REV.
10del #	LRWB 3-4H6-Z	SCALE NTS	TEVAPCO, I	NC.	SERIAL #	DATE 11/4/2025
2. MPT DEI FPT DEN BFW DE GVD DEI FLG DEN PE DEN(3. +UNIT W ACCESS 4. 3/4" [19m RECOMI 5. DIMENS 6. * - APPR USE FOI CONNEC 7. MAKE-UI 20 psi [13. 8. SERIES	MOTOR LOCATION NOTES MALE PIPE THREAD IOTES FEMALE PIPE THREAD NOTES BEVELED FOR WEL NOTES GROOVED JOTES FLANGE DIES PLAIN END EIGHT DOES NOT INCLUDE ORIES (SEE ACCESSORY D IMP) DIA. MOUNTING HOLES. MENDED STEEL SUPPORT I ONS LISTED AS FOLLOWS: OXIMATE DIMENSIONS DO R PRE-FABRICATION OF CTING PIPING. P WATER PRESSURE BY KPA] MIN, 50 psi [344 kPa] FLOW PIPING AND AUX. CR	AD DING  E DRAWINGS) . REFER TO DRAWING . ENGLISH FT IN [METRIC] [mm] NOT		FACE C		FACE D
	4" * →	1'-6" * [ 457 ]		FACE A		
(2) 4" [10 FLU 3 1/4" - [ 83 ] 2" [! OVE	TYP	( <sup>γ</sup> ) <del>  −</del>   <del>−</del> −	7'-3 1/4" [ 1297 ]  *  7'-3 1/4" [ 2216 ]  8 3/4" [ 919 ]  2 5/8" [ 67 ]  6 5/8" [ 167 ]	(2) 1/2" [15] FPT VENT  SERIES FLOW PIPING (BY OTHERS)  ACCESS DOOR  5'-6"  10'-1 7/8 [ 3096]	ACCESS DOOR  1" [25] MPT MAKE-UP	5'-3 3/8" [ 1610 ]
SHIPPING WEIGHT	2870 lbs+ [1305]	] kg+	OPERATING 4300 lbs+ [1955] kg+	HEAVIEST SECTION 2870 lbs+ [1305] kg+	NO. OF SHIPPING SECTIONS 1	RAWN BY: