DWG. # REV. UNIT **CLOSED CIRCUIT COOLER** WV050608-DRD-SF EVAPCO, INC. Evapco DATE 11/5/2025 MODEL # SERIAL # LRWB 5-4G6-Z NTS NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD **FACE C** FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO 5'-5/8" [1540] RECOMMENDED STEEL SUPPORT DRAWING FACE B FACE D 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN **PLAN VIEW** [METRIC] [mm] 6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF (M) CONNECTING PIPING. 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX 8. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS **FACE A** 1'-4 3/8" 「416] 2'-4" * [711] 6'-3" [1905] (2) 4" [100] BFW (2) 1/2" [15] FLÚID IN FPT VENT 4'-3" [1297] SERIES FLOW PIPING (2) 4" [100] BFW 2'-3" * [686] (BY OTHERS) FLUID OUT AUX. CROSSOVER DRAIN 7'-3 1/4" (BY OTHERS) 6'-7 3/4" [2026] 5 1/4" * ACCESS **DOOR** 3 1/4" TYP. → 3'-1/4" [919] 1'-8 1/8" [511] 1" [25] MP MAKE-UP 3" [80] MPT 5'-6" [1676] **ACCESS** OVERFLOW DOOR 2" [50] MPT 1'-1 5/8" [346] DRAIN 5'-5/8" [1540] **FACE A FACE B**

HEAVIEST SECTION

WEIGHT

4220 lbs+ [1915] kg+

SHIPPING

WEIGHT

OPERATING

WEIGHT

4220 lbs+ [1915] kg+

6660 lbs+ [3025] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: