


UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WLEP83606-DRD-SF	REV. -
MODEL # eco-LSWE 8P-3P36-Z	SCALE NTS		SERIAL #	DATE 8/23/2025

NOTES:

- (M)- FAN MOTOR LOCATION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- HEAVIEST SECTION IS COIL SECTION
- MAKE-UP WATER PRESSURE
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS

FACE B

PLAN VIEW




Diagram showing the plan view of the cooler with dimensions and connections. Key features include: SERIES FLOW PIPING (BY OTHERS), (2) ACCESS DOOR, (2) 3" [80] MPT OVERFLOW, (8) 4" [100] BFW FLUID IN, (8) 4" [100] BFW FLUID OUT, 2" [50] MPT MAKE-UP, 2" [50] MPT DRAIN, (8) 1/2" [15] FPT VENT, AUX. CROSSOVER DRAIN (BY OTHERS), and various dimensions in feet and inches with metric equivalents in brackets.

FACE C

FACE D




Diagram showing the side view of the cooler with dimensions and connections. Key features include: (8) 1/2" [15] FPT VENT, AUX. CROSSOVER DRAIN (BY OTHERS), and various dimensions in feet and inches with metric equivalents in brackets.

SHIPPING WEIGHT	33030 lbs+ [14985] kg+	OPERATING WEIGHT	48330 lbs+ [21925] kg+	HEAVIEST SECTION WEIGHT	11280 lbs+ [5120] kg+	NO. OF SHIPPING SECTIONS	3	DRAWN BY:	TLS
-----------------	------------------------	------------------	------------------------	-------------------------	-----------------------	--------------------------	---	-----------	-----