

UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WB3171212-DRD-ST	REV. -
MODEL # eco-ATWB 17-6J12	SCALE NTS		SERIAL #	DATE 2/14/2026

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS UPPER SECTION

3. MPT DENOTES MALE PIPE THREAD

FPT DENOTES FEMALE PIPE THREAD

BFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED

FLG DENOTES FLANGE

PE DENOTES PLAIN END

4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. MAKE-UP WATER PRESSURE

20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING


7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.

8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN

METRIC [mm]


FACE C



(2) ACCESS DOOR


FACE B

PLAN VIEW



FACE D

FACE A



1'-9 3/8"
[543]

3'-6"
[1067] *

1'-11 1/8"
[589]

3"
[76]

(2) 2" [50] MPT MAKE-UP

(2) 2" [50] MPT DRAIN

(2) 3" [80] MPT OVERFLOW

17'-4 1/8"
[5286]

4'-3/4"
[1238] *

2'-2 3/8"
[670] *

8'-10"
[2694]

13'-10 1/4"
[4223]

6"
[154] *

5'-1/4"
[1529]

2'-10 1/4"
[870]

1'-3"
[383]

8'-1/4"
[2445]

8'-1 1/4"
[2470]

8'-5 1/2"
[2578]

5 1/8"
[130]

1'-7/8"
[327]

(4) 1/2" [15] FPT VENT

1'-3 5/8"
[397]

11'-11 3/4"
[3651]

SHIPPING WEIGHT	37240 lbs+ [16895] kg+	OPERATING WEIGHT	51480 lbs+ [23355] kg+	HEAVIEST SECTION WEIGHT	16750 lbs+ [7600] kg+	NO. OF SHIPPING SECTIONS	4	DRAWN BY:	SLR
-----------------	------------------------	------------------	------------------------	-------------------------	-----------------------	--------------------------	---	-----------	-----