

EVAPCO, INC.






UNIT	CLOSED CIRCUIT COOLER	MODEL #	eco-ATWB 24-3K18	SCALE	N.T.S.	DWG. #	EG241806-DRA-ST	REV.	-	DATE	12/15/2025	SERIAL #	
------	-----------------------	---------	------------------	-------	--------	--------	-----------------	------	---	------	------------	----------	--

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- VENT PROVIDED ON CLOSED CIRCUIT COOLERS ONLY

**FACE 2
PLAN VIEW**



SHIPPING WEIGHT	48620 lbs+ [22055] kg+	OPERATING WEIGHT	74480 lbs+ [33785] kg+	HEAVIEST SECTION WEIGHT	20390 lbs+ [9250] kg+	NO. OF SHIPPING SECTIONS	4
-----------------	------------------------	------------------	------------------------	-------------------------	-----------------------	--------------------------	---