




UNIT		CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WB3242812-DRC-ST		REV. -										
MODEL # eco-ATWB 24-6N28		SCALE NTS			SERIAL #		DATE 3/31/2026										
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]																	
FACE B PLAN VIEW 					FACE C (4) ACCESS DOOR  FACE D FACE A 												
SHIPPING WEIGHT		123640 lbs+ [56085] kg+		OPERATING WEIGHT		175460 lbs+ [79590] kg+		HEAVIEST SECTION WEIGHT		27800 lbs+ [12610] kg+		NO. OF SHIPPING SECTIONS		6		DRAWN BY: SLR	