EVAPCO, INC. UNIT MODEL # DATE SERIAL # REV. N.T.S. TLEOP2436-DRA-ST **COOLING TOWER** LSTE-8P124L 9/6/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FOR VICTAULIC 7'-10" FACE 1 [2388] 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE **PLAN VIEW** 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 24'-1" [7341] FACE 2 7/8 [21] 94 [2388] 71 7/8 [1826] 71 7/8 [1826] 11 3/8 (2) 8 [200] BFW/GVD [290] INLET 74 7/8 [1901] (2) ACCESS DOOR ¬ 13'-6 1/4" [4120] 2 [50] MPT 3 [80] MPT MAKE-UP **OVERFLOW** 87 3/8 [2219] 35 1/2 [902] 2 [50] M₽T₁ T 21 3/8 ▼[543] DRAIN 7 5/8 24'-1" [7341] [194] 3 1/8 [79] 7 7/8 23 5/8 FACE 2 [199] [600] 40 3/8 10 [250] BFW/GVD [1026] 44 3/8 [1127] **OUTLET** 7'-10" [2388] FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 11890 lbs+ [5393] kg+ 19080 lbs+ [8655] kg+ 6890 lbs+ [3125] kg+ 3 WEIGHT WEIGHT WEIGHT