

UNIT		CONDENSER		EVAPCO, INC. 	DWG. #	WB3091806-DRC-ST	REV.	-	
MODEL #		eco-ATC-525A			SCALE	NTS		SERIAL #	DATE

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS UPPER SECTION

3. MPT DENOTES MALE PIPE THREAD

FPT DENOTES FEMALE PIPE THREAD

BFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED

FLG DENOTES FLANGE

PE DENOTES PLAIN END

4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. MAKE-UP WATER PRESSURE

20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING

7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.

8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN

METRIC [mm]

FACE B

PLAN VIEW

FACE C

ACCESS DOOR

ACCESS DOOR

FACE D

FACE A

1'-9 3/8" [543]

4'-3 1/4" [1238]

2'-2 3/8" [670]

6'-11 1/2" [2122]

11'-11 3/4" [3651]

1'-7 1/2" [495]

(2) 4" [100] PE

REFRIG IN

REFRIG OUT

6" [154]

5'-1 1/4" [1529]

1'-3" [383]

2" [50] MPT MAKE-UP

1'-11 1/8" [589]

3" [76]

2" [50] MPT DRAIN

5 1/4" [133]

4 1/4" [108]

5'-7 1/4" [1708]

8'-5 1/2" [2578]

3" [80] MPT OVERFLOW

FACE B

1'-7/8" [327]

1'-5" [430]

18'-0" [5486]

FACE A

SHIPPING WEIGHT	18280 lbs+ [8295] kg+	OPERATING WEIGHT	24390 lbs+ [11065] kg+	HEAVIEST SECTION WEIGHT	15490 lbs+ [7030] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY:	SLR
-----------------	-----------------------	------------------	------------------------	-------------------------	-----------------------	--------------------------	---	-----------	-----