

|                               |                                                                                                                         |          |                               |          |
|-------------------------------|-------------------------------------------------------------------------------------------------------------------------|----------|-------------------------------|----------|
| UNIT<br>CLOSED CIRCUIT COOLER | <div> <div>EVAPCO, INC.</div>  </div> |          | DWG. #<br>WX409063606P-DRA-ST | REV<br>- |
| MODEL #<br>ESW4 9-33H6-LP     | SCALE<br>NTS                                                                                                            | SERIAL # | DATE:<br>5/9/2026             |          |


  

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES.  
REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
8. \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING

**FACE B**  
**PLAN VIEW**


**FACE C**




**FACE D**

**FACE A**

**FACE B**



(M)  
 \* 11" [279]  
 4" [100] BFW FLUID IN  
 2" [50] MPT MAKE-UP  
 2" [50] MPT DRAIN  
 2'-3" [686]  
 3 3/8" [86]  
 4 1/4" [107]  
 5 1/4" [132]  
 5'-11 7/8" [1826]  
 4" [100] BFW FLUID OUT  
 3" [80] MPT OVERFLOW  
 \* 1'-7 1/2" [495]  
 \* 2'-2 3/8" [670]  
 1'-6 3/8" [465]  
 2'-0 5/8" [625]  
 \* 2'-6 1/2" [773]



1'-0 7/8" [327]  
 7'-8 1/8" [2340]  
 15'-2 3/4" [4643]  
 7'-6 5/8" [2303]  
 1'-5" [432]  
 8'-5 1/2" [2578]  
 1/2" [15] FPT VENT  
 ACCESS DOOR (M)

**FACE A**

|                                         |                                          |                                                 |                               |                  |
|-----------------------------------------|------------------------------------------|-------------------------------------------------|-------------------------------|------------------|
| SHIPPING WEIGHT<br>7000 lbs+ [3180] kg+ | OPERATING WEIGHT<br>9880 lbs+ [4485] kg+ | HEAVIEST SECTION WEIGHT<br>4770 lbs+ [2160] kg+ | NO. OF SHIPPING SECTIONS<br>2 | DRAWN BY:<br>AWT |
|-----------------------------------------|------------------------------------------|-------------------------------------------------|-------------------------------|------------------|