

UNIT COOLING TOWER		EVAPCO, INC. evapco	DWG. # T3121248-DRD-ST	REV. -
MODEL # AT 112-4K12	SCALE NTS		SERIAL #	DATE 9/20/2025

NOTES:
1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL SUPPORT
DRAWING
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE B

PLAN VIEW

FACE C

FACE D

FACE A

FACE B

1'-3 1/4" [387]

7" [178]

2" [51]

10'-4" [3150]

15'-6 1/4" [4731]

5'-2 1/4" [1581]

11'-10" [3607]

3/8" [9]

FACE A

5'-11 7/8" [1826]

8" [200] BFW/GVD INLET

2" [50] MPT MAKE-UP

10'-2" [3099]

2'-1 1/4" [641]

1'-4 7/8" [429]

7 1/4" [184]

3 5/8" [92]

5 1/4" [133]

9" [229]

5'-11 7/8" [1826]

11'-11 3/4" [3651]

8" [200] BFW/GVD OUTLET

3" [80] FPT OVERFLOW

3" [80] FPT DRAIN

SHIPPING WEIGHT	8480 lbs+ [3850] kg+	OPERATING WEIGHT	14690 lbs+ [6665] kg+	HEAVIEST SECTION WEIGHT	6080 lbs+ [2760] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY:	KDS
-----------------	----------------------	------------------	-----------------------	-------------------------	----------------------	--------------------------	---	-----------	-----