

UNIT COOLING TOWER		EVAPCO, INC. 	DWG. # T3040424-DRJ-ST	REV. -
MODEL # AT 14-2E4	SCALE NTS		SERIAL #	DATE 4/25/2026

NOTES:
1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO
RECOMENDED STEEL SUPPORT DRAWING.
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE B

PLAN VIEW

FACE C

ACCESS DOOR

FACE D

FACE A

1'-3/4" [324]

(M)

2'-1/8" [613]

6'-5" [1956]

4" [100] MPT INLET

9'-6 1/2" [2908]

4" [100] MPT OUTLET

1" [25] MPT MAKE-UP

5 7/8" [149]

2" [50] MPT OVERFLOW

2" [50] MPT DRAIN

3'-1 1/2" [953]

1'-7 3/4" [502]

10 1/4" [260]

2'-1/4" [616]

5 1/8" [130]

4'-1/2" [1232]

FACE B

1'-1" [330]

4 1/2" [114]

6'-3" [1905]

3'-11 7/8" [1216]

FACE A

SHIPPING WEIGHT1080 lbs+ [490] kg+

OPERATING WEIGHT1710 lbs+ [780] kg+

HEAVIEST SECTION WEIGHT730 lbs+ [335] kg+

NO. OF SHIPPING SECTIONS2

DRAWN BY:KWC