

UNIT COOLING TOWER		EVAPCO, INC. evapco	DWG. # T3121248-DRD-ST	REV. -
MODEL # AT 112-4I12	SCALE NTS		SERIAL #	DATE 3/24/2026

NOTES:
1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL SUPPORT
DRAWING
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE B

PLAN VIEW

FACE C

FACE D

FACE A

FACE B

PLAN VIEW

FACE C

FACE D

FACE A

SHIPPING WEIGHT

8360 lbs+ [3795] kg+

OPERATING WEIGHT

14570 lbs+ [6610] kg+

HEAVIEST SECTION WEIGHT

5960 lbs+ [2705] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

KDS