

UNIT	CONDENSER
MODEL #	eco-PMRC-855

EVAPCO, INC.




DWG. # CEWR122404-DRA-ST

REV -
SERIAL #
DATE: 2/19/2026

NOTES:


- (M) - FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,
50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING.

FACE C



FACE D

FACE B
PLAN VIEW



FACE B

FACE A

SHIPPING
WEIGHT

28870 lbs+ [13100] kg+

OPERATING
WEIGHT

38330 lbs+ [17390] kg+

HEAVIEST SECTION
WEIGHT

10790 lbs+ [4895] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: JLG