

UNIT	CONDENSER	
MODEL #	eco-PMRC-819	SCALE NTS

# EVAPCO, INC.




DWG. # CEWRTM2404-DRA-ST

REV -

## NOTES



- (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,  
50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
7. \* - APPROXIMATE DIMENSIONS DO NOT  
USE FOR PRE-FABRICATION OF CONNECTING PIPING

### **FACE C**



**FACE B**

## FACE D



[2551]  
**FACE B**

## FACE A

**SHIPPING  
WEIGHT**

26240 lbs+ [11905] kg+

## OPERATING WEIGHT

33860 lbs+ [15360] kg+

## HEAVIEST SECTION WEIGHT

10440 lbs+ [4740] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: **JLG**