UNIT					DWG.#	REV
CONDENSER			EVAPCO, INC. Evapeo		CEWR121806-DRA-ST	-
MODEL#	eco-PMRC-888	NTS	LVAPCO		SERIAL#	DATE: 10/17/2025
2. MPT DEN FPT DEN BFW DEN GVD DEN FLG DEN PE DENC ACCESSO 4. 3/4" [19I RECOMM 5. MAKE-UF 50 psi [3 6. DIMENSI ENGLIS [METRI] 7. * - APPR	I MOTOR LOCATION. IOTES MALE PIPE THREAD OTES FEMALE PIPE THREAD NOTES BEVELED FOR WELDING NOTES GROOVED OTES FLANGE ITES PLAIN END VEIGHT DOES NOT INCLUDE PRIES (SEE ACCESSORY DRAWINGS). INM JOIA. MOUNTING HOLES. REFER TO NENDED STEEL SUPPORT DRAWING. P WATER PRESSURE 20 psi [137 kPa] MIN, 44 kPa] MAX. ONS LISTED AS FOLLOWS: H FT-IN C] [mm] OXIMATE DIMENSIONS DO NOT PRE-FABRICATION OF CONNECTING PIPING.			FACE B PLAN VIEW	FACE C	FACE D
2'-5"[7; <u>+</u> 1'-8"	OVERSIZED ACCESS DOORS  MPT 5 1/8" [130]  80] MPT DRAIN  37]  [508] 3 7/8" [98]  5'-0 3/8" [1534]	8 5/8" * 1743] O REFRIG IN REFRIG OUT 3"[80] MPT OVERFLOW	-1'-10 1/4" [565] *  13'-7 1/2" [4153]  9'-11" [3023] *	5'-1 1/8" [1553] 8'-6 3/8" [2600]	18'-0 1/8" [5490]	
11'-10 3/8" [3616]						
FACE B						
SHIPPING WEIGHT	28190 lbs+ [12790] kg+	OPERATING WEIGHT	34990 lbs+ [15875] kg+	HEAVIEST SECTION 19170 lbs+ [8700] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: JLG